



冷藏循环浴“Frigiterm-TFT-10-S”和“Frigiterm-TFT-30-S”

可调温度范围: $-10\text{ }^{\circ}\text{C} - 100\text{ }^{\circ}\text{C}$. 稳定性: $0\text{ }^{\circ}\text{C} - 100\text{ }^{\circ}\text{C}$, $\pm 0,1\text{ }^{\circ}\text{C}$ / $-10\text{ }^{\circ}\text{C}$, $\pm 0,1\text{ }^{\circ}\text{C}$

可调温度范围: $-30\text{ }^{\circ}\text{C} - 100\text{ }^{\circ}\text{C}$. 稳定性: $0\text{ }^{\circ}\text{C} - 100\text{ }^{\circ}\text{C}$, $\pm 0,1\text{ }^{\circ}\text{C}$ / $-30\text{ }^{\circ}\text{C}$, $\pm 0,2\text{ }^{\circ}\text{C}$

设定误差: $\pm 1\text{ }^{\circ}\text{C}$. 分辨率: $0,1\text{ }^{\circ}\text{C}$

安全保护:

符合STANDARD DIN 12876. 手动复位的可调手
安全过温恒温器, 带有低液位传感器保护

特点

保持最高温度的最大工作容积: **8 L**

AISI 304不锈钢顶部, 盖子和内胆

配有带入口和出口连接器的泵, 用于内部和外部液体循环

排水龙头位于装置的侧面

密封压缩机安装在防振支架上

RS-232 接口用于连接打印机和计算机

型号

	Part No.	Capacity litres	Control range $^{\circ}\text{C}$	Height / Width / Depth (usable) cm	Height / Width / Depth (exterior) cm	Pump Pressure / Flowrate H ₂ O	Power W	Compressor power H.P.	Weight Kg
FRIGITERM-10-S	3000552	8	-10 + 100	12 20 14	66 36 46	150 mbar-12 l/min	1150	1/8	28
FRIGITERM-30-S	3000553	8	-30 + 100	12 20 14	66 36 46	150 mbar-12 l/min	1460	3/8	30

